


DRAINAGE - QUICK SIZING

 <p>UNILIFT AP35</p>	The selection and sizing illustration is based on an inner diameter of a 1½" pipe and secure a self cleaning velocity inside the pipe.		
		AP35.40.06	AP35.40.08
	Head\Distance		
	9 m		Max. 30 m
	8 m		Max. 75 m
	7 m	Max. 35 m	Max. 120 m
	6 m	Max. 80 m	Max. 165 m
	5 m	Max. 130 m	Max. 215 m
	4 m	Max. 170 m	Max. 255 m
	3 m	Max. 220 m	Max. 305 m
2 m	Max. 265 m	Max. 350 m	

 <p>UNILIFT AP35B</p>	The selection and sizing illustration is based on an inner diameter of a 2" pipe and secure a self cleaning velocity inside the pipe.		
		AP35B.50.06	AP35B.50.08
	Head\Distance		
	9 m		Max. 15 m
	8 m		Max. 75 m
	7 m	Max. 20 m	Max. 135 m
	6 m	Max. 80 m	Max. 195 m
	5 m	Max. 140 m	Max. 260 m
	4 m	Max. 200 m	Max. 320 m
	3 m	Max. 260 m	Max. 385 m
2 m	Max. 325 m	Max. 440 m	

DRAINAGE - QUICK SIZING

 <p>UNILIFT AP50</p>	The selection and sizing illustration is based on an inner diameter of a 2" pipe and secure a self cleaning velocity inside the pipe.		
		AP50.50.08	AP50.50.11
	Head\Distance		
	9 m		Max. 55 m
	8 m		Max. 115 m
	7 m	Max. 45 m	Max. 175 m
	6 m	Max. 105 m	Max. 235 m
	5 m	Max. 165 m	Max. 295 m
	4 m	Max. 225 m	Max. 360 m
	3 m	Max. 285 m	Max. 405 m
2 m	Max. 350 m	Max. 480 m	

 <p>UNILIFT AP50B</p>	The selection and sizing illustration is based on an inner diameter of a 2" pipe and secure a self cleaning velocity inside the pipe.			
		AP50B.50.08	AP50B.50.11	AP50B.50.15
	Head\Distance			
	14 m			Max. 65 m
	12 m			Max. 190 m
	11 m		Max. 25 m	Max. 250 m
	10 m		Max. 85 m	Max. 310 m
	9 m		Max. 145 m	Max. 370 m
	8 m	Max. 45 m	Max. 205 m	Max. 430 m
	6 m	Max. 165 m	Max. 330 m	*
5 m	Max. 225 m	Max. 390 m	*	
4 m	Max. 285 m	Max. 450 m	*	
3 m	Max. 345 m	*	*	
2 m	Max. 490 m*	Max. 740 m*	Max. 1060 m*	

*The pumps shall not operate for longer time with this Head